Technical datasheet

Flexam EF 10/2 0+S24 black AS FR / 35Sh

Ammeraal Beltech
Innovation & Service in Belting

Article code: SBFL589738

General information	
Product group	Synthetic Belts
Industry segment	Airports; Logistics: Distribution & warehousing
Main product feature	Antistatic, Flame retardant
Indication of use	Flat, Rollers, Troughed, Slider bed

Belt construction					
Tension layer		polyester, flexible			
Number of plies		2			
Top side	material	Flexam, PVC			
	finish	profile, S24 Basket weave			
	color	black			
Bottom side	material	fabric, polyester			
	finish	bare fabric			
	color	natural			

Characteristics		
Food Grade (FG)	no	
Antistatic (AS)	yes	ISO 21178
High conductive (HC)	no	
Flame-retardant	yes	ISO 340
	no	
ATEX approval	no	

Technical data								
Hardness	ISO 868	top side	35A	Shore				
Force at 1% elongation (static)	ISO 21181		10	N/mm	57.1	lbs/in.		
Thickness	AB method KV.002	total	2.40	mm	0.09	in.		
		top cover	0.80	mm	0.03	in.		
Weight	AB method KV.004		2.3	kg/m²	0.47	lbs/ft²		
Operating temperature	continuous	from / to	-15 / 80	°C	5 / 176	°F		
	short	from / to	-15 / 100	°C	5 / 212	°F		
Minimum pulley diameter	flexing		40	mm	1.57	in.		
	backflexing		70	mm	2.76	in.		
Manufacturing width	standard		3200	mm	125.98	in.		
	maximum		3200	mm	125.98	in.		

Fabrication

Hot splicing is always preferable. Glueing can only be done when the belt is exposed to normal temperature and the humidity is not excessive. For the working method, consult the splice information and the equipment literature. Apply the recommended splice as indicated in the seperate information.

Additional information

This sheet contains typical values, which apply to a temperature of approx. 20 °C (68 °F), unless otherwise stated, individual data may differ.

We recommend to keep the belt tension to a practical working minimum to maximize the service life of the belt and machine parts.

Always protect belts from sunlight/UV-radiation, avoid temperatures below 10°C and above 40°C, dust and dirt. Store belts in a cool and dry place and if possible in their original packaging.

For details consult 'Storage and handling instructions' or contact our specialist.