**Technical datasheet** 

## Flexam EX 10/2 0+A32 black AS NL

Article code: SBFL589793



General information				
Product group	Synthetic Belts			
Industry segment	Airports; Logistics: Distribution & warehousing; Building materials: Insulation			
Main product feature	Antistatic, Low noise			
Indication of use	Slider bed, Rollers, Flat			

Belt construction					
Tension layer		polyester, stable			
Number of plies		2			
Top side	material	Flexam, PVC			
	finish	profile, A32 Fine rib profile			
	color	black			
Bottom side	material	fabric, polyester			
	finish	bare fabric			
	color	natural			

Characteristics			
Food Grade (FG)	no		
Antistatic (AS)	yes	ISO 21178	
High conductive (HC)	no		
Flame-retardant	no		
	no		
ATEX approval	no		

Technical data							
Hardness	ISO 868	top side	35A	Shore			
Force at 1% elongation (static)	ISO 21181		10	N/mm	57.1	lbs/in.	
Thickness	AB method KV.002	total	2.80	mm	0.11	in.	
		top cover	1.30	mm	0.05	in.	
Weight	AB method KV.004		2.5	kg/m²	0.51	lbs/ft²	
Operating temperature	continuous	from / to	-15 / 80	°C	5 / 176	°F	
	short	from / to	-15 / 100	°C	5 / 212	°F	
Minimum pulley diameter	flexing		25	mm	0.98	in.	
	backflexing		40	mm	1.57	in.	
Manufacturing width	standard		2000	mm	78.74	in.	
	maximum		3000	mm	118.11	in.	

## **Fabrication**

Hot splicing is always preferable. Glueing can only be done when the belt is exposed to normal temperature and the humidity is not excessive. For the working method, consult the splice information and the equipment literature. Apply the recommended splice as indicated in the seperate information.

## **Additional information**

This sheet contains typical values, which apply to a temperature of approx. 20 °C (68 °F), unless otherwise stated, individual data may differ.

We recommend to keep the belt tension to a practical working minimum to maximize the service life of the belt and machine parts.

Always protect belts from sunlight/UV-radiation, avoid temperatures below 10°C and above 40°C, dust and dirt. Store belts in a cool and dry place and if possible in their original packaging.

For details consult 'Storage and handling instructions' or contact our specialist.