

Ropanyl EM05 6/1 00+02 white M2 AS FG

Article code: SBRY579891

General information

Product group	Synthetic Belts
Industry segment	Food: Confectionary & candy
Main product feature	Antistatic, Foodgrade, Laterally stable
Indication of use	Slider bed, Flat

Belt construction

Tension layer		polyester, extra stable
Number of plies		1
Top side	material	Ropanyl, TPU
	finish	smooth, M2 Matt finish
	color	white
Bottom side	material	Ropanol, PUR
	finish	impregnated fabric
	color	transparent

Characteristics

Food Grade (FG)	yes	EC 1935/2004, EU 10/2011; FDA
Antistatic (AS)	yes	ISO 21178
High conductive (HC)	no	
ATEX approval	no	

Technical data

Hardness	ISO 868	top side	85A Shore	
Force at 1% elongation (static)	ISO 21181		6 N/mm	34.26 lbs/in.
Thickness	AB method KV.002	total	1.05 mm	0.04 in.
		top cover	0.25 mm	0.01 in.
Weight	AB method KV.004		1.4 kg/m ²	0.29 lbs/ft ²
Heat transfer coefficient			190 W/(m ² .K)	33.48 BTU/(h.ft ² .°F)
Operating temperature	continuous	from / to	-20 / 90 °C	-4 / 194 °F
	short	from / to	-30 / 110 °C	-22 / 230 °F
Minimum pulley diameter	flexing		10 mm	0.39 in.
	backflexing		20 mm	0.79 in.
Manufacturing width	standard		2100 mm	82.68 in.
	maximum		3000 mm	118.11 in.

Fabrication

Hot splicing is always preferable. Glueing can only be done when the belt is exposed to normal temperature and the humidity is not excessive. For the working method, consult the splice information and the equipment literature. Apply the recommended splice as indicated in the separate information.

Additional information

This sheet contains typical values, which apply to a temperature of approx. 20 °C (68 °F), unless otherwise stated, individual data may differ.

We recommend to keep the belt tension to a practical working minimum to maximize the service life of the belt and machine parts.

Always protect belts from sunlight/UV-radiation, avoid temperatures below 10°C and above 40°C, dust and dirt. Store belts in a cool and dry place and if possible in their original packaging.

For details consult 'Storage and handling instructions' or contact our specialist.